F1-CLAMP-4B



KwikClamp™ Hanger for 1/4 in superflexible coaxial cable, quadruple stack; includes hardware

Product Classification

Product Type	Hanger kit	
Product Brand	KwikClamp™	
Ordering Note	ANDREW® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box	
General Specifications		
Cables per Hanger	1	
Color	Black	
Hanger Type	KwikClamp™ hanger	
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8- 25 mm	

Dimensions

Maximum Stack Height	4
Height	22 mm 0.866 in
Width	22 mm 0.866 in
Length	171 mm 6.732 in
Compatible Diameter, maximum	9 mm 0.354 in
Compatible Diameter, minimum	7 mm 0.276 in
Nominal Size	1/4 in
Hanger Spacing, maximum	1.83 m 6.004 ft
Electrical Specifications	
Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB
Material Specifications	

Material Type

Engineered plastic | Stainless steel

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025

F1-CLAMP-4B

Mechanical Specifications

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

-40 °C to +70 °C (-40 °F to +158 °F)
≥500 hours in salt spray chamber
Five times cable weight
\geq 100 hours exposure in accelerated UV life chamber

Packaging and Weights

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025