## L5-CLAMP-4B



KwikClamp™ Hanger for 7/8 in coaxial cable, quadruple stack; includes hardware

#### **Product Classification**

Product TypeHanger kitProduct BrandKwikClamp™

Ordering Note ANDREW® standard product in Europe, the Middle East, and

Africa | Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger

**Color** Black

**Hanger Type** KwikClamp™ hanger

Mounting 3-25 mm angle iron | 3-25 mm flat plate | Round Member 8-

25 mm

**Dimensions** 

Maximum Stack Height 1

 Height
 235 mm | 9.252 in

 Width
 45 mm | 1.772 in

 Length
 32 mm | 1.26 in

 Compatible Diameter, maximum
 28 mm | 1.102 in

 Compatible Diameter, minimum
 26 mm | 1.024 in

Nominal Size 7/8 in

Hanger Spacing, maximum 1.83 m | 6.004 ft

**Electrical Specifications** 

Return Loss Effect, maximum0.1 dBDTF Effect, maximum0.1 dB

Material Specifications

Material Type Engineered plastic | Stainless steel

ANDREW® an Amphenol company

# L5-CLAMP-4B

### Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ 

**Corrosion Resistance, minimum with no degredation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 15.5 cm | 6.102 in

 Width, packed
 30.5 cm | 12.008 in

 Length, packed
 35.5 cm | 13.976 in

**Included** Hardware

Packaging quantity 24

**Weight, gross** 7 kg | 15.432 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

