760256743 | C-144-LA-8W-M12YL/25G/GRP/D



TeraSPEED® Single Jacket/Single GRP Armor, Gel, Indoor/Outdoor Stranded Loose Tube cable. Provides Rodent Resistance. Tube Colours Red, Green, 10 x Natural

• GRP armor is strong yet flexible, providing additional crush and rodent protection

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America	
Portfolio	CommScope®	
Product Type	Fiber indoor/outdoor cable	
Product Series	C-LA	
General Specifications		
Armor Type	Non-metallic rods	
Cable Type	Stranded loose tube	
Construction Type	Armored	
Subunit Type	Gel-filled	
Jacket Color	Yellow	
Jacket Marking	Meters	
Jacket Marking Method	Laser	
Jacket Marking Text	COMMSCOPE GB OPTICAL CABLE [MID] 144 X G652D EN50575 CLASS D ULSZH [MM/YY] [Serial number] [metre mark]	
Subunit, quantity	12	
Fibers per Subunit, quantity	12	
Total Fiber Count	144	
Dimensions		
Buffer Tube/Subunit Diameter	2.5 mm 0.098 in	
Diameter Over Jacket	21.7 mm 0.854 in	
Material Specifications		
Inner Jacket Material	Low Smoke Zero Halogen (LSZH)	

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



760256743 | C-144-LA-8W-M12YL/25G/GRP/D

Mechanical Specifications

Minimum Bend Radius, loaded	432 mm 17.008 in	
Minimum Bend Radius, unloaded	324 mm 12.756 in	
Tensile Load, long term, maximum	2000 N 449.618 lbf	
Tensile Load, short term, maximum	6000 N 1,348.854 lbf	
Compression	40 N/mm 228.406 lb/in	
Compression Test Method	IEC 60794-1 E3	
Impact	15 N-m 132.761 in lb	
Impact Test Method	IEC 60794-1 E4	
Strain	See long and short term tensile loads	
Strain Test Method	IEC 60794-1 E1	
Twist	5 cycles	
Twist Test Method	IEC 60794-1 E7	
Optical Specifications		
Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2	

Environmental Specifications

Installation temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	IEC 60794-1-2
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s1
EN50575 CPR Cable EuroClass Droplets Rating	d2
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Aerial, lashed Buried
Flame Test Method	IEC 60332-1-2
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5

Environmental Test Specifications

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

COMMSCOPE°

760256743 | C-144-LA-8W-M12YL/25G/GRP/D

Heat Age

Temperature Cycle

Temperature Cycle Test Method

Packaging and Weights

Cable weight

0 °C to +85 °C (+32 °F to +185 °F) -40 °C to +70 °C (-40 °F to +158 °F) IEC 60794-1 F1

452 kg/km | 303.73 lb/kft

Included Products

CS-8W-LT

 TeraSPEED® G652D/G657A1 Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

