

# F-CLAMP-E-1B



KwikClamp™ Hanger for power & fiber cables, 9-12 mm, single stack; includes hardware

## Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	ANDREW® standard product in Europe, the Middle East, and Africa   Minimum order quantity (MOQ) is 1 box

## General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron   3–25 mm flat plate   Round Member 8-25 mm

## Dimensions

Maximum Stack Height	1
Height	111 mm   4.37 in
Width	32 mm   1.26 in
Length	46 mm   1.811 in
Compatible Cable Diameter Range	9–12 mm
Compatible Diameter, maximum	12 mm   0.472 in
Compatible Diameter, minimum	9 mm   0.354 in
Hanger Spacing, maximum	1.83 m   6.004 ft

## Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

## Material Specifications

Material Type	EPDM rubber   Engineered plastic   Stainless steel
---------------	--

# F-CLAMP-E-1B

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 15.5 cm | 6.102 in

**Width, packed** 30.5 cm | 12.008 in

**Length, packed** 35.5 cm | 13.976 in

**Included** Hardware

**Packaging quantity** 81

**Weight, gross** 7.5 kg | 16.535 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power