## 760251256 | CMC-74-36C



# CMC-74 Equipment and Battery Cabinet NiCd, 3-String, 3 kW Air Conditioner, DC

The cabinet is designed to combine wireless telecom power equipment and NiCad batteries into one cabinet. Equipment ranges from DC power system, Fiber slack tray, cell site router and other servers equipped by customer. This cabinet provide mechanical and environmental protection for the equipment inside. Cooling of active equipment is achieved by DC rated 3000W Air Conditioner.

- Excellent Thermal Performance to be compatible with both Heat Exchanger and Air Conditioner.
- Provides enough space for the Power system and other network servers.
- Provides option requirements for security/access control via Puck Lock system.
- Provides flexible access for the cable entrance.
- Provides flexible heater solution for the cold ambient application.
- Provides flexible configurations to give best in class maximum equipmentrack mounting space (Up to 24 total RU)
- Platform products to share many parts including plinth, solar shield, and hybridcable storage units.
- Excellent cable management system.

#### **Product Classification**

Regional Availability Latin America | North America

**Product Type** Macro cell site enclosure

Product Series CMC

#### General Specifications

Access Bottom: Power compartment | Rear Wall: Hybrid Cables | Side Wall: Power or other cables

compartment

**Batteries Supported** 3 strings of Nicad batteries from Multiple OEM

**Battery Storage** 2 battery shelves for holding up to 3 Nicad battery strings

Cabinet Type Baseband cabinet | Battery back-up cabinet | Transmission cabinet

**Capacity** 500W Heater built in Air Conditioner

**Color** Light Gray (RAL 7035) | Other RAL-colors available at additional cost

Cooling DC Rated 3000W Air Conditioner Or 300W/k Thermosiphon unit for equipment compartment

**Door Security**Quarter turn lock, puck lock system for rear door | Swing handle, puck lock system for front door

Mounts directly to steel dunnage with supplied 1/2" hardware | Mounts to concrete pad with customer

supplied anchors | Optional 6" plinth

**Noise Emission, maximum** 60 dBA

Rack Capacity, total 24RU (Horizontal 20RU +Vertical 4RU)



## 760251256 | CMC-74-36C

Rack Type EIA 19 in | EIA 23 in


**Dimensions** 

 Height
 1,879.6 mm | 74 in

 Width
 914.4 mm | 36 in

 Depth
 939.8 mm | 37 in

#### Dimension Drawing



### **Electrical Specifications**

Input Power Supply 125Volt Receptable/Outlet | 20AMP GFCI Outlet | Compliant with UL943 Self-Test Requirement

Alarm Output Dry contacts

Cooling Capacity 3000 W

**dc Distribution Type**Universally supports multiple -48VDC OEM Power Plants and Distribution

Voltage -48 Vdc

#### Cabinet Mounting



## 760251256 | CMC-74-36C



#### Material Specifications

Finish Powder coated | UV resistant

Material Type Aluminum

#### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+46 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +115  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Qualification Standards ANSI/UL 62638-1 | ETL 4007237 | GR-487 | IEC 60529, IP55 | Seismic rating, zone 4 | UL

1801

#### Packaging and Weights

**Weight, net** 384.646 kg | 848 lb

