810010280/DB | B-008-CN-8G-M08BK/19G



Fiber OSP cable, LightScope® ZWP Blown Single Jacket All-Dielectric Outdoor Central Tube Construction, Singlemode G.657.A2, Gel-filled, Meters jacket marking, Black jacket color

Product Classification

Regional Availability Europe

Product Type CommScope®

Fiber OSP cable

Product Series B-CN

General Specifications

Cable Type Central tube, all dielectric | Microcable

Construction TypeNon-armoredSubunit TypeGel-filled

Filler, quantity 0

Inner Jacket Color White
Jacket Color Black
Jacket Marking Method Inkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE BLW 810010280/DB 8 x G657A2 SM [SERIAL

NUMBER] [METER MARK]

Subunit, quantity 1

Fibers per Subunit, quantity 8

Total Fiber Count 8


Dimensions

Buffer Tube/Subunit Diameter1.9 mm0.075 inDiameter Over Jacket2.5 mm0.098 in

Representative Image



810010280/DB | B-008-CN-8G-M08BK/19G



Material Specifications

Jacket Material Nylon

Mechanical Specifications

Minimum Bend Radius, loaded30 mm1.181 inMinimum Bend Radius, storage coils30 mm1.181 inMinimum Bend Radius, unloaded30 mm1.181 inTensile Load, long term, maximum75 N | 16.861 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method IEC 60794-1-21 E3

Flex 25 cycles

 Impact
 2 N-m | 17.701 in lb

 Impact Test Method
 IEC 60794-1-21 E4

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-21 E1

Twist 10 cycles

Twist Test Method IEC 60794-1-21 E7

Optical Specifications

Fiber Type G.657.A2 | G.657.A2

COMMSC PE®

810010280/DB | B-008-CN-8G-M08BK/19G

IEC 60794-1-2 | IEC 60794-5-10

Environmental Specifications

Cable Qualification Standards

-10 °C to +60 °C (+14 °F to +140 °F) **Operating Temperature**-20 °C to +60 °C (-4 °F to +140 °F)

Storage Temperature $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Environmental Space Air-blown, microduct

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5

Environmental Test Specifications

Low High Bend Test Method IEC 60794-1-21 E11

Temperature Cycle $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Temperature Cycle Test Method IEC 60794-1-22 F1

Packaging and Weights

Cable weight 6.4 kg/km | 4.301 lb/kft

Included Products

CS-8G-LT – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T

G.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



CS-8G-LT

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G. 657.A2, B2)

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm ±0.7 µm **Cladding Diameter Tolerance** 0.7 % Cladding Non-Circularity, maximum 249 µm **Coating Diameter (Colored) Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm Core/Clad Offset, maximum 0.5 µm

Proof Tensile Stress 100,000 psi (0.69 GPa)

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 1 turn
 0.50 dB @ 1,550 nm
 1 1.00 dB @ 1,625 nm

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.10 dB @ 1,550 nm
 1 0.20 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.03 dB @ 1,550 nm
 0.10 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

COMMSCOPE®

CS-8G-LT

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1302 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.25 dB/km @ 1,550 nm | 0.33 dB/km @ 1,385

nm | 0.36 dB/km @ 1,310 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

 $\textbf{Mode Field Diameter} \hspace{1.5cm} 8.6~\mu m \ @ 1,310~nm \hspace{0.2cm} | \hspace{0.2cm} 9.8~\mu m \ @ 1,550~nm$

Mode Field Diameter Tolerance $\pm 0.4 \ \mu m$ @ 1310 nm | $\pm 0.5 \ \mu m$ @ 1550 nm

Polarization Mode Dispersion Link Design Value, maximum 0.06 ps/sqrt(km)

Standards Compliance ITU-T G.657.A2 | ITU-T G.657.B2

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

