

Fiber OSP cable, LightScope® ZWP Blown Micro Single Jacket, 36 fiber, All-Dielectric Stranded Loose Tube Arid-Core™ Construction, Gel-filled, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	B-LN


## General Specifications

<b>Cable Type</b>	Stranded loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	3
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Subunit, quantity</b>	3
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	36

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	1.25 mm   0.049 in
<b>Diameter Over Jacket</b>	4.6 mm   0.181 in

## Representative Image



## Material Specifications

**Jacket Material** High density polyethylene (HDPE)

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	95 mm   3.74 in
<b>Minimum Bend Radius, unloaded</b>	60 mm   2.362 in
<b>Tensile Load, long term, maximum</b>	400 N   89.924 lbf
<b>Tensile Load, short term, maximum</b>	1000 N   224.809 lbf
<b>Compression</b>	5 N/mm   28.551 lb/in
<b>Compression Test Method</b>	IEC 60794-1-21 E3
<b>Flex</b>	25 cycles
<b>Flex Test Method</b>	IEC 60794-1 E6
<b>Impact</b>	1 N-m   8.851 in lb
<b>Impact Test Method</b>	IEC 60794-1-21 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1-21 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	IEC 60794-1-21 E7

## Optical Specifications

**Fiber Type** G.652.D and G.657.A1

## Environmental Specifications

<b>Installation temperature</b>	-15 °C to +40 °C (+5 °F to +104 °F)
<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Cable Qualification Standards</b>	IEC 60794-5-10
<b>Environmental Space</b>	Air-blown, microduct
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F4

## Environmental Test Specifications

<b>Drip</b>	70 °C   158 °F
<b>Drip Test Method</b>	IEC 60794-1-21 E14
<b>Heat Age</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Heat Age Test Method</b>	IEC 60794-1-22 F9
<b>Temperature Cycle</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-22 F1

## Packaging and Weights

<b>Cable weight</b>	19 kg/km   12.767 lb/kft
---------------------	--------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber  
8W-250um

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable