


# MC-RMHD-1245-3

---



Universal Ring Mount, Heavy Duty 3-sector, 12 in to 45 in OD

## Product Classification

**Product Type** Universal ring mount

## General Specifications

**Mounting** Monopole, 304.8–1270 mm (12–50 in) OD

**Sectors, quantity** 3

## Dimensions

**Height** 381 mm | 15 in

**Mounting Diameter, maximum** 1,143 mm | 45 in

**Mounting Diameter, minimum** 304.8 mm | 12 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Mount | Threaded rod

**Packaging quantity** 1

**Weight, net** 149.323 kg | 329.2 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

# MC-RMHD-1245-3

---

