## 5226303 | P3® 625 JCASS SM MT

75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground



 \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

#### **Product Classification**

Regional Availability North America

Product Type Coaxial hardline cable

Product Brand P3®

**Government Funding**Build America Buy America (BABA) compliant\*

**Warranty** One year

General Specifications

Cable Type625 SeriesConstruction TypeSwagedJacket ColorBlack

#### **Dimensions**

**Cable Length** 731.52 m | 2400 ft **Diameter Over Center Conductor, nominal** 3.48 mm | 0.137 in **Diameter Over Dielectric, nominal** 14.351 mm | 0.565 in **Diameter Over Inner Jacket, nominal** 17.653 mm | 0.695 in **Diameter Over Jacket, nominal** 21.59 mm | 0.85 in **Diameter Over Outer Conductor, nominal** 15.875 mm | 0.625 in 0.762 mm | 0.03 in Inner Jacket Thickness, nominal 0.762 mm | 0.03 in Jacket Thickness, nominal **Outer Conductor Thickness, nominal** 0.762 mm | 0.03 in

**Electrical Specifications** 

**Capacitance** 50.197 pF/m | 15.3 pF/ft



# 5226303 | P3® 625 JCASS SM MT

dc Resistance Note Nominal values based on a standard condition of 20 °C (68 °F)

dc Resistance, Inner Conductor, nominal2.756 ohms/km | 0.84 ohms/kftdc Resistance, Loop, nominal3.609 ohms/km | 1.1 ohms/kftdc Resistance, Outer Conductor, nominal0.853 ohms/km | 0.26 ohms/kft

Jacket Spark Test Voltage5000 VacNominal Velocity of Propagation (NVP)87 %

Operating Frequency Band 5–3000 MHz

**Structural Return Loss** 24 dB @ 1003-1218 MHz | 24 dB @ 1219-1794 MHz | 30 dB @ 5-1002

MHz

**Structural Return Loss, Grade N** ≥24 dB @ 1003−1218 MHz | ≥24 dB @ 1219−1794 MHz | ≥30 dB @ 5−1002

MHz

#### **Attenuation**

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.43	0.13
55.0	1.48	0.45
85.0	1.84	0.56
204.0	2.92	0.89
211.0	3.02	0.92
250.0	3.28	1
300.0	3.54	1.08
350.0	3.87	1.18
400.0	4.17	1.27
450.0	4.43	1.35
500.0	4.69	1.43
550.0	4.92	1.5
600.0	5.18	1.58
750.0	5.84	1.78
865.0	6.33	1.93
1002.0	6.92	2.11
1218.0	7.62	2.32
1500.0	8.74	2.66





# 5226303 | P3® 625 JCASS SM MT

1794.0	9.7	2.96
1800.0	9.72	2.96
2000.0	10.34	3.15
2200.0	10.95	3.34
2500.0	11.81	3.6
2700.0	12.37	3.77
3000.0	13.19	4.02

## Material Specifications

Center Conductor Material Copper-clad aluminum

**Dielectric Material** Foam PE

Jacket Material PE

Outer Conductor Material Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded114.3 mm4.5 inPulling Tension, maximum215.456 kg475 lb

## **Environmental Specifications**

 Corrosion Protection
 Migraheal®

 Environmental Space
 Buried

Packaging and Weights

Packaging Type Reel

**Weight, gross** 278.287 kg/km | 187 lb/kft

## Regulatory Compliance/Certifications

# AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliantUK-ROHSCompliant





