

Fiber indoor/outdoor cable, Gel-filled Central Tube, 4 fiber, Multimode OM5, Meters jacket marking, Black jacket color

## Product Classification

Regional Availability	Asia   Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-CN


## General Specifications

Cable Type	Central loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Fibers per Subunit, quantity	4
Total Fiber Count	4

## Dimensions

Buffer Tube/Subunit Diameter	2.8 mm   0.11 in
Diameter Over Jacket	7 mm   0.276 in

## Representative Image



## Mechanical Specifications

Minimum Bend Radius, loaded	140 mm   5.512 in
Minimum Bend Radius, unloaded	70 mm   2.756 in
Tensile Load, long term, maximum	800 N   179.847 lbf
Tensile Load, short term, maximum	1800 N   404.656 lbf
Compression	15 N/mm   85.652 lb/in
Compression Test Method	IEC 60794-1-2 E3
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-2-E1

## Optical Specifications

Fiber Type	OM5
------------	-----

## Optical Specifications, Wavelength Specific

Attenuation, maximum	1.00 dB/km @ 1,300 nm   3.00 dB/km @ 850 nm
----------------------	---

## Environmental Specifications

Installation temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)
Flame Test Method	IEC 60332-1

Environmental Test Specifications

Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1-2 F1

Packaging and Weights

Cable weight	58 kg/km   38.974 lb/kft
--------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable