

FL2-S780AG039-DU00

FL2000 Fiber Termination Panel, 144 LC/UPC, singlemode, 5RU, 23 in, putty white, pre-terminated with OSP cable, 39 meters, Stub tail at far end

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with OSP cable
Product Series	FL2000

General Specifications

Functionality	Patching
Adapter Packs Included, quantity	12
Cable Exit Location	Upward
Cable Stub Type	IFC
Color	Putty white
Color, front	Putty white
Growth Configuration	Fully loaded
Interface, front	LC
Interface Feature, front	Standard
Interface, rear	Stub tail
Patching Capacity, maximum	144
Rack Type	EIA 23 in
Rack Units	5
Shelf Movement	Hinged
Splicing Capacity, maximum	0
Total Ports, quantity	144

Dimensions

Height	222.25 mm 8.75 in
Width	584.2 mm 23 in
Depth	256.54 mm 10.1 in
Cable Stub Length	39 m 127.953 ft

FL2-S780AG039-DU00

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

FL2-S780AG039-DU00

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

