

## Base Product



### Fiber Optic Patch Cord, Multi-fiber, Singlemode

- Breakout types: Double-ended breakouts or breakouts-to-stub end
- Fiber counts: 4, 8, 12, 24, 36, 48, 72, 96 and 144 stranded fibers
- Use ratings: Plenum- or Dual Rated (LSZH/Riser)
- Connector: 22 combinations using ultra-polished or angle-polished MPO, SC, LC and stub end
- Breakout lengths: 20 inches to 120 inches
- Available with or without pulling socks
- All fiber optic cable is tested in accordance with GR-409
- All single fiber connectors are tested to GR-326 performance specifications
- All MPO fiber connectors are tested to GR-1435 performance specifications

Pre-terminated 1.2 mm multi-fiber cable assemblies, to increase density in your optical distribution frames (ODFs) and accelerate fiber deployment. Our cable assemblies designed for a wide variety of in-building applications and can be configured for your specific needs. These multi-fiber cable assemblies provide fast plug-and-play turn up of new customers and services. They are designed for use with all ODF systems, including CommScope's popular NG4 frame, enabling you to support greater fiber density without sacrificing manageability.

These in-building assemblies use no metallic strength members and are designed to meet the fire-resistant characteristics required in a variety of central office applications. All assembly components have passed the rigorous requirements of the Telcordia GR specifications.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Europe   Latin America   Middle East/Africa   North America
<b>Product Type</b>	Fiber distribution cable assembly

