

# PULSAR-EDGE-CNTRL

---



## PowerShift® High Power Pulsar Edge Controller

### Product Classification

<b>Product Type</b>	Module
<b>Product Brand</b>	PowerShift®
<b>Product Series</b>	V2

### General Specifications

<b>Backplane Interfaces</b>	10/100 Base-T Ethernet   One Galaxy Protocol (GP) RS485 bus
<b>Front Panel Display</b>	Interface to shelf mounted interactive display

### Dimensions

<b>Height</b>	41.402 mm   1.63 in
<b>Width</b>	18.288 mm   0.72 in
<b>Depth</b>	345.44 mm   13.6 in

### Electrical Specifications

<b>Electrical Safety Standard</b>	UL60950-UL/cUL with CB report
-----------------------------------	-------------------------------

### Environmental Specifications

<b>Relative Humidity</b>	95%, non-condensing
<b>Ambient Temperature</b>	-40 °C   -40 °F   65 °C   149 °F
<b>Mean Time Between Failures (MTBF) at Temperature</b>	300,000 h @ 25 °C
<b>Standards Compliance</b>	CE-compliant when used with the PS-R-1 Shelf

### Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

### Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# PULSAR-EDGE-CNTRL

---

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

