810010238/DB/GS | D-576-LA-8W-F24NS/200/GS



Fiber OSP cable, Single Jacket/Single Armor, 576 fiber, Gel-Free, Stranded Loose Tube, Singlemode G.652.D and G.657.A1, 200um fiber, Feet jacket marking, Black jacket color

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series D-LA

General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

Construction Type Armored

Subunit Type Gel-free

Jacket Color Black

Jacket Marking Feet

Subunit, quantity 24

Fibers per Subunit, quantity 24

Total Fiber Count 576

Dimensions


Buffer Tube/Subunit Diameter 2.5 mm | 0.098 in

Diameter Over Jacket 19.6 mm | 0.772 in

Representative Image



810010238/DB/GS | D-576-LA-8W-F24NS/200 /GS



Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded294 mm11.575 inMinimum Bend Radius, unloaded196 mm7.717 inTensile Load, long term, maximum800 N179.847 lbfTensile Load, short term, maximum2700 N606.984 lbf

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 4.4 N-m | 38.943 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 297 m | 974.409 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1 | OM5, LazrSPEED® wideband

COMMSCOPE®

810010238/DB/GS | D-576-LA-8W-F24NS/200/GS

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-22 °F to} + 158 °F)$ Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-40 °F to} + 158 °F)$ Storage Temperature $-40 \,^{\circ}\text{C to} + 75 \,^{\circ}\text{C (-40 °F to} + 167 °F)$

Cable Qualification Standards ANSI/ICEA S-87-640 | EN 187105 | Telcordia GR-20

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Qualification Method ANSI/ICEA S-87-640

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 275 kg/km | 184.791 lb/kft

Included Products

CS-8W-200UM-LT – 200 Micron Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

