AL5NM-PSA



Type N Male Positive Stop™ for 7/8 in AVA5-50 cable

Product Classification

Product TypeWireless and radiating connector

Product Brand HELIAX® | Positive Stop™

Product Series AVA5-50 | AVA5RK-50

Ordering Note CommScope® non-standard product

General Specifications

Body Style Straight

Cable Family AL5-50 | AVA5-50

Inner Contact Attachment Method Captivated

Inner Contact Plating Silver

Interface N Male

Mounting Angle Straight

Outer Contact Attachment Method Ring-flare

Outer Contact Plating Trimetal

Pressurizable No

Dimensions


Length 63.25 mm | 2.49 in

Diameter 37.08 mm | 1.46 in

Nominal Size 7/8 in

Outline Drawing





Electrical Specifications

3rd Order IMD at Frequency -116 dBm @ 910 MHz
3rd Order IMD Test Method Two +43 dBm carriers

Insertion Loss Coefficient, typical 0.05

Average Power at Frequency 0.6 kW @ 900 MHz

Cable Impedance50 ohmConnector Impedance50 ohmdc Test Voltage2000 VInner Contact Resistance, maximum2 mOhmInsulation Resistance, minimum5000 MOhmOperating Frequency Band0 - 5200 MHzOuter Contact Resistance, maximum0.3 mOhm

Peak Power, maximum 10 kW
RF Operating Voltage, maximum (vrms) 707 V
Shielding Effectiveness -130 dB

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

50–1000 MHz 1.023 38.89

COMMSCOPE®

AL5NM-PSA

1010-2200 MHz	1.025	38.17
2210-3000 MHz	1.036	35.05
3010-4000 MHz	1.074	28.95
4010-5200 MHz	1.135	23.98

Mechanical Specifications

Attachment Durability 25 cycles

Connector Retention Tensile Force1,334.47 N | 300 lbfConnector Retention Torque8.14 N-m | 72.001 in lbCoupling Nut Proof Torque4.52 N-m | 39.997 in lbCoupling Nut Retention Force444.82 N | 100 lbf

Coupling Nut Retention Force Method MIL-C-39012C-3.25, 4.6.22

Insertion Force 66.72 N | 15 lbf

Insertion Force Method MIL-C-39012C-3.12, 4.6.9

Interface Durability 500 cycles

Interface Durability Method IEC 61169-16:9.5

Mechanical Shock Test Method MIL-STD-202F, Method 213B, Test Condition C

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)Storage Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature $20 \, ^{\circ}\text{C} \mid 68 \, ^{\circ}\text{F}$ Average Power, Ambient Temperature $40 \, ^{\circ}\text{C} \mid 104 \, ^{\circ}\text{F}$

Corrosion Test Method MIL-STD-1344A, Method 1001.1, Test Condition A

Immersion Depth 1 m

Immersion Test Mating Unmated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method MIL-STD-202F, Method 106F

Thermal Shock Test Method MIL-STD-202F, Method 107G, Test Condition A-1, Low Temperature -55 °C

Vibration Test Method IEC 60068-2-6

Water Jetting Test Mating Unmated

Water Jetting Test Method IEC 60529:2001, IP66



AL5NM-PSA

Packaging and Weights

Weight, net 133.89 g | 0.295 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss Coefficient, typical 0.05√ freq (GHz) (not applicable for elliptical waveguide)

Immersion Depth Immersion at specified depth for 24 hours

