
## 760119545 | P-072-MZ-8W-F12YL



Fiber indoor cable, TeraSPEED® Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, Singlemode G.652.D and G.657.A, 72 fiber multi-unit with 12 fiber subunits, Yellow jacket color, Feet cable marking

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** P-MZ

General Specifications

Armor Type Interlocking aluminum

Cable Type MPO trunk cable

Construction Type Armored

Fiber Type, quantity 72

Fibers per Subunit, quantity 12

Jacket Color Yellow

Jacket Marking Feet

Subunit Type Gel-free

**Subunit, quantity** 6

**Total Fiber Count** 72

**Dimensions** 

**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in


**Diameter Over Armor** 17.15 mm | 0.675 in

**Diameter Over Jacket** 19.2 mm | 0.756 in

Representative Image



# 760119545 | P-072-MZ-8W-F12YL



### Mechanical Specifications

Minimum Bend Radius, loaded288 mm11.339 inMinimum Bend Radius, unloaded192 mm7.559 inTensile Load, long term, maximum400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

**Compression** 85 N/mm | 485.363 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 132 m | 433.071 ft

**Optical Specifications** 

**Fiber Type** G.652.D and G.657.A1, TeraSPEED® | OS2 | OS2

**Environmental Specifications** 

**Installation temperature** 0 °C to +70 °C (+32 °F to +158 °F)

COMMSC PE®

## 760119545 | P-072-MZ-8W-F12YL

**Operating Temperature**  $0 \, ^{\circ}\text{C to } +70 \, ^{\circ}\text{C (} +32 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$ 

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFCP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend** 0 °C to +70 °C (+32 °F to +158 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 308 kg/km | 206.966 lb/kft

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



#### Included Products

CS-8W-MP - TeraSPEED® OS2 Singlemode Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

