## CM-606-96



#### Chain Mount Kit, 16 ft chain, includes pipe

### **Product Classification**

Product Type	Chain mount kit

### General Specifications

Chains, quantity	2
Pipe, quantity	6
Sectors, quantity	6


#### **Dimensions**

Height	152.4 mm   6 in
Width	203.2 mm   8 in
Length	2,438.4 mm   96 in
Chain Length	4,902.2 mm   193 in
Pipe Length	2,438.4 mm   96 in
Mounting Diameter, maximum	1524 mm   60 in
Mounting Diameter, minimum	355.6 mm   14 in
Pipe Outer Diameter	60.96 mm   2.4 in
Mounting Circumference, maximum	4,775.2 mm   188 in
Mounting Circumference, minimum	1,117.6 mm   44 in



## CM-606-96

#### Outline Drawing



#### Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

**Wind Rating Criteria** One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Chains | Plain end pipes

**COMMSCOPE®** 

## CM-606-96

Packaging quantity

1

Weight, net

124.7 kg | 274.916 lb

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

CM-606-B – Chain Mount Base Kit, 14 in stand-off 16 ft chain MT-651-96 – Plain End Pipe, 2-3/8 in OD x 96 in .120" A500C

46Ksi

#### \* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code



## CM-606-B



#### Chain Mount Base Kit, 14 in stand-off 16 ft chain

#### **Product Classification**

Product Type Chain mount kit

#### General Specifications


Chains, quantity 2
Pipe, quantity 0
Sectors, quantity 6

#### Dimensions

Height 152.4 mm | 6 in Width 203.2 mm | 8 in Length 203.2 mm | 8 in **Chain Length** 4,902.2 mm | 193 in 1524 mm | 60 in Mounting Diameter, maximum **Mounting Diameter, minimum** 355.6 mm | 14 in **Pipe Outer Diameter** 60.96 mm | 2.4 in **Mounting Circumference, maximum** 4,775.2 mm | 188 in **Mounting Circumference, minimum** 635 mm | 25 in

## CM-606-B

### Outline Drawing



### Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

**Wind Rating Criteria** One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Brackets | Chains | Hardware

Page 5 of 8

# CM-606-B

Packaging quantity

**Weight, net** 36.3 kg | 80.028 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

1





#### Plain End Pipe, 2-3/8 in OD x 96 in .120" A500C 46Ksi

#### **Product Classification**

Product Type Plain end pipe

#### General Specifications

Pipe, quantity 1

#### **Dimensions**

 Height
 60.96 mm | 2.4 in

 Width
 60.96 mm | 2.4 in

 Length
 2,438.4 mm | 96 in

 Pipe Length
 2,438.4 mm | 96 in

 Pipe Outer Diameter
 60.96 mm | 2.4 in

 Material Thickness
 3.048 mm | 0.12 in

#### Material Specifications

Material Type A500 | Hot dip galvanized steel

Material Grade C

Material Strength 46 KSI

#### Packaging and Weights

**Included** Pipe **Packaging quantity** 1

**Weight, net** 10 kg | 22.046 lb

#### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

**COMMSCOPE®** 

# MT-651-96

ROHS UK-ROHS Compliant/Exempted
Compliant/Exempted



COMMSCOPE®