CM-60D-96



Chain Mount Kit, 16 ft chain, includes pipe

Product Classification

General Specifications

Chains, quantity	2
Pipe, quantity	2
Sectors, quantity	2


Dimensions

Height	152.4 mm 6 in
Width	203.2 mm 8 in
Length	2,438.4 mm 96 in
Chain Length	4,902.2 mm 193 in
Pipe Length	2,438.4 mm 96 in
Mounting Diameter, maximum	1524 mm 60 in
Mounting Diameter, minimum	203.2 mm 8 in
Pipe Outer Diameter	60.96 mm 2.4 in
Mounting Circumference, maximum	4,775.2 mm 188 in
Mounting Circumference, minimum	635 mm 25 in



CM-60D-96

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Criteria One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Chains | Plain end pipes

Packaging quantity

Weight, net 53.4 kg | 117.727 lb

COMMSCOPE®

CM-60D-96

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

CM-60D-B – Chain Mount Base Kit, 16 ft chain

MT-651-96 – Plain End Pipe, 2-3/8 in OD x 96 in .120" A500C

46Ksi

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code



CM-60D-B



Chain Mount Base Kit, 16 ft chain

Product Classification

Product Type Chain mount kit


General Specifications

Chains, quantity 2
Pipe, quantity 0
Sectors, quantity 2

Dimensions

Height 152.4 mm | 6 in Width 203.2 mm | 8 in Length 203.2 mm | 8 in **Chain Length** 4,902.2 mm | 193 in 1524 mm | 60 in Mounting Diameter, maximum **Mounting Diameter, minimum** 203.2 mm | 8 in **Pipe Outer Diameter** 60.96 mm | 2.4 in **Mounting Circumference, maximum** 4,775.2 mm | 188 in 635 mm | 25 in **Mounting Circumference, minimum**

CM-60D-B



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Criteria One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Chains

Page 5 of 8

CM-60D-B

Packaging quantity

1

Weight, net 23 kg | 50.706 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code





Plain End Pipe, 2-3/8 in OD x 96 in .120" A500C 46Ksi

Product Classification

Product Type Plain end pipe

General Specifications

Pipe, quantity 1

Dimensions

 Height
 60.96 mm | 2.4 in

 Width
 60.96 mm | 2.4 in

 Length
 2,438.4 mm | 96 in

 Pipe Length
 2,438.4 mm | 96 in

 Pipe Outer Diameter
 60.96 mm | 2.4 in

 Material Thickness
 3.048 mm | 0.12 in

Material Specifications

Material Type A500 | Hot dip galvanized steel

Material Grade C

Material Strength 46 KSI

Packaging and Weights

Included Pipe **Packaging quantity** 1

Weight, net 10 kg | 22.046 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

COMMSCOPE®

MT-651-96

ROHS UK-ROHS Compliant/Exempted
Compliant/Exempted



COMMSCOPE®