

8-port sector antenna, 4X 617-894 and 4X 1695-2690 MHz, 65°HPBW, 2X RET

- Antenna design optimized to offer high gain performances
- Broadband performance 617-894 MHz and 1695-2690 MHz

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, mid band	4
RF Connector Quantity, low band	4
RF Connector Quantity, total	8

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10-30 Vdc
Internal RET	Low band (1) Mid band (1)
Power Consumption, active state, maximum	10 W
Power Consumption, idle state, maximum	2 W
Protocol	3GPP/AISG 2.0 (Single RET)
Dimensions	

Width

640 mm | 25.197 in

Page 1 of 6

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 15, 2024




Depth

Length

235 mm | 9.252 in

2438 mm | 95.984 in

Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG No.	AISG RET UID
R1	617-894	1 - 2	1	AISG1	CPxxxxxxxxxxxxxR1
R2	617-894	3 - 4		AISGT	CPXXXXXXXXXXXXXXXXXXXXX
¥1	1695-2690	5 - 6	2	AISG1	CPxxxxxxxxxxxxxXXXXXXXXXXXXXXXXXXXXXXXX
Y2	1695-2690	7 - 8	2	AISGI	

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance

Operating Frequency Band

1695 – 2690 MHz | 617 – 894 MHz

Page 2 of 6

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 15, 2024

50 ohm



Polarization	±45°
Total Input Power, maximum	900 W @ 50 °C

Electrical Specifications

	R1,R2	R1,R2	Y1,Y2	Y1,Y2	Y1,Y2	Y1,Y2	Y1,Y2
Frequency Band, MHz	617-698	698-894	1695-1880	1850-1990	1920-2200	2300-2500	2500-2690
RF Port	1-4	1-4	5-8	5-8	5-8	5-8	5-8
Gain, dBi	16.2	17	19.9	20.1	20.3	20.2	20.7
Beamwidth, Horizontal, degrees	68	62	65	59	61	67	57
Beamwidth, Vertical, degrees	10.2	8.6	4.2	4.1	3.9	3.4	3.2
Beam Tilt, degrees	2-12	2-12	2-9	2-9	2-9	2-9	2-9
USLS (First Lobe), dB	15	16	17	16	17	17	19
Front-to-Back Ratio at 180°, dB	30	33	37	38	36	35	34
Front-to-Back Total Power at 180° ± 30°, dB	22	23	30	31	29	27	26
CPR at Boresight, dB	16	16	25	23	19	21	27
CPR at Sector, dB	8	8	4	4	5	7	7
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	250	250	200	200	200	200	200

Electrical Specifications, BASTA

Frequency Band, MHz	617-698	698-894	1695-1880	1850-1990	1920-2200	2300-2500	2500-2690
Gain by all Beam Tilts, average, dBi	15.7	16.3	19	19.6	19.7	19.3	19.8
Gain by all Beam Tilts Tolerance, dB	±0.4	±0.6	±0.7	±0.3	±0.5	±0.6	±0.7
Beamwidth, Horizontal Tolerance, degrees	±6	±4	±5	±4	±9	±9	±10
Beamwidth, Vertical Tolerance, degrees	±0.7	±1	±0.2	±0.2	±0.3	±0.3	±0.2
USLS, beampeak to 20° above	15	15	12	14	15	13	11

Page 3 of 6

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 15, 2024



beampeak, dB

Mechanical Specifications

Wind Loading @ Velocity, frontal	987.0 N @ 150 km/h (221.9 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	291.0 N @ 150 km/h (65.4 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	1,257.0 N @ 150 km/h (282.6 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	616.0 N @ 150 km/h (138.5 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	744 mm 29.291 in
Depth, packed	384 mm 15.118 in
Length, packed	2590 mm 101.969 in
Weight, gross	80.7 kg 177.913 lb
Weight, net	59.5 kg 131.175 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

BSAMNT-3F

Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

Page 4 of 6

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 15, 2024



BSAMNT-3F



Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

Product Classification	
Product Type	Fixed tilt mounting kit
General Specifications	
Application	Outdoor
Color	Silver
Dimensions	
Compatible Diameter, maximum	115 mm 4.528 in
Compatible Diameter, minimum	60 mm 2.362 in
Weight, net	5.6 kg 12.346 lb
Material Specifications	
Material Type	Galvanized steel

Packaging and Weights

Included	Brackets Hardware
Packaging quantity	1
Weight, gross	5.8 kg 12.787 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 5 of 6

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 10, 2024







Page 6 of 6

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 10, 2024

