Twin Hybrid Combiner



Product Classification

Product TypeHybrid combinerProduct BrandUltraBand™

General Specifications

AISG Carrier 2176 KHz ± 100 ppm

Color Gray

Connector Interface7-16 DIN FemaleModularityTwo-pack twinMountingPole | WallMounting Pipe HardwareBand clamps

Dimensions

 Height
 181 mm | 7.126 in


 Width
 371 mm | 14.606 in

 Depth
 86.5 mm | 3.406 in

 Ground Screw Diameter
 6 mm | 0.236 in

Outline Drawing





Electrical Specifications

3rd Order IMD Test Method Two +43 dBm carriers

3rd Order IMD, typical-160 dBcdc Pass-throughBranch 2Lightning Surge Current10 kA

Lightning Surge Current Waveform 8/20 waveform

Electrical Specifications, AISG

 dc Current, maximum
 2.5 A

 Insertion Loss, maximum
 0.5 dB

 Return Loss, minimum
 16 dB

Electrical Specifications, Branch 1



Input Power, RMS	150 W
Isolation, typical	30 dB

Operating Frequency Band 698 – 2700 MHz

Port DesignationPort 1Insertion Loss Ripple, maximum $\pm 0.4 \, dB$ Return Loss, minimum20 dB

Electrical Specifications, Branch 2

 Coupling
 3.1 dB

 Coupling Tolerance
 ±0.5 dB

 Input Power, PEP
 3000 W

 Input Power, RMS
 150 W

 Isolation, typical
 30 dB


Operating Frequency Band 698 – 2700 MHz

 Port Designation
 Port 2

 Insertion Loss Ripple, maximum
 ±0.4 dB

 Return Loss, minimum
 20 dB

Block Diagram



Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+65 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+149 \,^{\circ}\text{F}$)

ANDREW® an Amphenol company

Ingress Protection Test Method IEC 60529:2001, IP67

Packaging and Weights

IncludedMounting hardwareWeight, net9 kg | 19.842 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

