

# SRC9-U5A101BN001-US



NOVUX™ Specialty Range Closure 10, splice only, no adapters, no splitters, Stranded (4F) splice holder, Ribbon (12F) splice holder, TelSplice connector, black, 2x CR cable retention clip, Build America Buy America (BABA)

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information
- \*CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	Asia   EMEA   Latin America   North America
<b>Regional Availability Note</b>	Contact your local CommScope representative for specific availability
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	NOVUX™
<b>Product Series</b>	SRC10
<b>Government Requirements</b>	Build America Buy America (BABA) coming soon*

## General Specifications

<b>Cable Capacity, Drop</b>	2 Flat 8.0 x 4.5 mm (0.30 x 0.17 in)   2 Round 2–6.2 mm (0.08–0.24 in)
<b>Cable Ports Quantity, total</b>	2 round ports
<b>Cable Sealing Type</b>	Compressed gel
<b>Cable Termination Attachments, quantity</b>	2
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	In-line
<b>Color</b>	Black
<b>Location of Manufacturing</b>	Coming soon
<b>Mounting</b>	Handhole   Partially buried   Pedestal   Wall/Pole Mount, mounting kit included

# SRC9-U5A101BN001-US

---

<b>Network Area Type</b>	Drop
<b>Port, quantity</b>	2
<b>Splice Tray Included, quantity</b>	1
<b>Splicing Capacity, Mass Fusion, maximum</b>	12
<b>Splicing Capacity, maximum</b>	4
<b>Splicing Capacity, Single Fusion, maximum</b>	4
<b>Splicing Type, Supported</b>	Single fusion
<b>Splitter Type</b>	No splitter

## Dimensions

<b>Width</b>	76 mm   2.992 in
<b>Depth</b>	26 mm   1.024 in
<b>Length</b>	210 mm   8.268 in
<b>Cable Entry Drop Port Diameter</b>	6 mm ( 0.24 in) mm

## Material Specifications

<b>Material Type</b>	Impact-resistant polymer
----------------------	--------------------------

## Optical Specifications

<b>Fiber Type</b>	G.657.A1   G.657.A2   G.657.B3
-------------------	--------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Above ground   Below ground   Direct burial
<b>Qualification Standards</b>	IEC 60529, IP68 + 1 m waterhead   IEC 61753-1, category G
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Weight, net</b>	0.157 kg   0.346 lb