

RT-NF13-4-120



PIM-Guard High Capacity Non-Penetrating Roof Frame with Optimized Antenna Spacing 13 ft face, four 2-7/8 in OD x 120 in pipes

Product Classification

Product Type	Non-penetrating roof frame
Product Brand	PIM-guard

General Specifications

Mounting	Non-penetrating
Pipe, quantity	4

Dimensions

Height	3,048 mm 120 in
Face Width	3.962 m 13 ft
Width	3,962.4 mm 156 in
Length	2.377 m 7.8 ft
Pipe Length	3,048 mm 120 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type	Hot dip galvanized steel
---------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Ballast tray Frame Plain end pipes (4)
Packaging quantity	1
Weight, net	537.4 kg 1,184.763 lb

RT-NF13-4-120

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

