## RT-NF13-B



PIM-Guard High Capacity Non-Penetrating Roof Frame with Optimized Antenna Spacing 13 ft face, Base Frame Only

local ANDREW representative

Product Classification	
Product Type	Non-penetrating roof frame
Product Brand	PIM-guard
General Specifications	
Mounting	Non-penetrating
Pipe, quantity	0
Dimensions	
Height	2,252.98 mm   88.7 in
Face Width	3.962 m   13 ft
Width	3,962.4 mm   156 in
Length	2.377 m   7.8 ft
Pipe Length	0 mm   0 in
Face Support Pipe Diameter	73.152 mm   2.88 in
Pipe Outer Diameter	73.152 mm   2.88 in
Material Specifications	
Material Type	Hot dip galvanized steel
Mechanical Specifications	
Wind Rating	For Specifications, please contact your
Wind Rating Test Method	TIA/EIA-222
Packaging and Weights	
Included	Ballast tray   Frame

Included	Ballast tray   Frame
Packaging quantity	1
Weight, net	387.77 kg   854.885 lb

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

## \* Footnotes

Wind Rating

BWS–Base Wind Speed; FBC–Florida Building Code

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025