

Fiber OSP cable, LazrSPEED 550 Mini Single Jacket All-Dielectric, High Tensile Strength, Gel-Filled, Multi-mode OM4, 12 fiber, Stranded Loose Tube, Meters jacket marking, Black jacket color, Provides Rodent Resistance

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®
Product Type Fiber OSP cable

Product Series O-LN

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Filler, quantity 5

Jacket Color Black

Jacket Marking Method Inkjet

Jacket Marking Text COMMSCOPE OPTICAL CABLE [MID] OM4 MM (FIBER COUNT) FIBER [SERIAL NUMBER]

[MM/YYYY] [Meter marking] m

Subunit, quantity 1

Fibers per Subunit, quantity 12


Total Fiber Count 12

Dimensions

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket11.6 mm | 0.457 in

Representative Image





Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded174 mm | 6.85 inMinimum Bend Radius, unloaded116 mm | 4.567 inTensile Load, long term, maximum1350 N | 303.492 lbfTensile Load, short term, maximum4500 N | 1,011.641 lbfCompression22 N/mm | 125.623 lb/inCompression Test MethodFOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 1345 m | 4,412.73 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

Environmental Specifications



Installation temperature $-10 \,^{\circ}\text{C to } +50 \,^{\circ}\text{C (} +14 \,^{\circ}\text{F to } +122 \,^{\circ}\text{F)}$ Operating Temperature $-30 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (} -22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-87-640 | EN 187105 | IEC 60794-1-2

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Drip 70 °C | 158 °F

Drip Test Method FOTP-81 | IEC 60794-1 E14

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-15 \,^{\circ}\text{C}$ to $+40 \,^{\circ}\text{C}$ (+5 $^{\circ}\text{F}$ to +104 $^{\circ}\text{F}$)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 115 kg/km | 77.276 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable