

## Self-Supporting Tenable Outdoor Drop Cable

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Hybrid cable, fiber and tone-wire                                   |
| <b>Product Series</b>        | O-DF  |


## General Specifications

|                                     |                           |
|-------------------------------------|---------------------------|
| <b>Cable Type</b>                   | Drop                      |
| <b>Construction Type</b>            | Non-armored               |
| <b>Subunit Type</b>                 | Gel-free                  |
| <b>Jacket Color</b>                 | Black                     |
| <b>Jacket Marking</b>               | Feet                      |
| <b>Location of Manufacturing</b>    | Claremont, North Carolina |
| <b>Subunit, quantity</b>            | 1                         |
| <b>Fibers per Subunit, quantity</b> | 1                         |
| <b>Total Fiber Count</b>            | 1                         |

## Dimensions

|                                     |                   |
|-------------------------------------|-------------------|
| <b>Height Over Jacket</b>           | 2.8 mm   0.11 in  |
| <b>Buffer Tube/Subunit Diameter</b> | 0.9 mm   0.035 in |
| <b>Diameter Over Jacket</b>         | 7.6 mm   0.299 in |

## Representative Image



## Material Specifications

**Jacket Material** PE

## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 60 mm   2.362 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 60 mm   2.362 in                      |
| <b>Tensile Load, long term, maximum</b>  | 400 N   89.924 lbf                    |
| <b>Tensile Load, short term, maximum</b> | 1350 N   303.492 lbf                  |
| <b>Compression</b>                       | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 35 cycles                             |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 1.4 N-m   12.391 in lb                |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |

## Optical Specifications

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

## Environmental Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Installation temperature</b>      | -30 °C to +60 °C (-22 °F to +140 °F) |
| <b>Operating Temperature</b>         | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Storage Temperature</b>           | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Cable Qualification Standards</b> | ANSI/ICEA S-110-717                  |
| <b>Environmental Space</b>           | Aerial, self-support   Buried        |
| <b>Jacket UV Resistance</b>          | UV stabilized                        |
| <b>Water Penetration</b>             | 24 h                                 |
| <b>Water Penetration Test Method</b> | FOTP-82   IEC 60794-1 F5             |

## Environmental Test Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Cable Freeze</b>                  | -2 °C   28.4 °F                      |
| <b>Cable Freeze Test Method</b>      | FOTP-98   IEC 60794-1 F15            |
| <b>Drip</b>                          | 70 °C   158 °F                       |
| <b>Drip Test Method</b>              | FOTP-81   IEC 60794-1 E14            |
| <b>Heat Age</b>                      | -40 °C to +85 °C (-40 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                       |
| <b>Low High Bend</b>                 | -30 °C to +60 °C (-22 °F to +140 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11            |
| <b>Temperature Cycle</b>             | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1              |

## Packaging and Weights

|                     |                              |
|---------------------|------------------------------|
| <b>Cable weight</b> | 20.673 kg/km   13.892 lb/kft |
|---------------------|------------------------------|

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable