

UGBKIT-0412



Copper Ground Buss Bar, 1/4 in x 4 in x 12 in (6.4 mm x 101.6 mm x 304.8 mm)

Product Classification

Product Type	Grounding bar
Ordering Note	CommScope® standard product (Global)

Dimensions

Height	101.6 mm 4 in
Length	304.8 mm 12 in
Material Thickness	6.35 mm 0.25 in
Hole Size	7/16 in 7/16 in x 5/8 in
Hole Distance, center to center	19.05 mm 0.75 in

Material Specifications

Material Type	Copper
----------------------	--------

Packaging and Weights

Height, packed	454.66 mm 17.9 in
Width, packed	248.92 mm 9.8 in
Length, packed	50.8 mm 2 in
Included	Galvanized angle adapter Grounding bar Insulators Mounting brackets Universal hardware
Packaging quantity	1
Weight, gross	3.36 kg 7.408 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

UGBKIT-0412

UK-ROHS

Compliant



Included Products

- GB-HK-DPU – Universal Buss Bar Hardware Kit, UL467 Compliant

GB-HK-DPU



Universal Buss Bar Hardware Kit, UL467 Compliant

Product Classification

Product Type	Attachment kit
Ordering Note	CommScope® standard product in the United States and Canada

General Specifications

Accessories	Grounding Bars
--------------------	----------------

Packaging and Weights

Height, packed	170.18 mm 6.7 in
Width, packed	129.54 mm 5.1 in
Length, packed	99.06 mm 3.9 in
Included	Angle adapters Insulators, Mounting brackets Universal hardware
Packaging quantity	1
Weight, gross	2.6 kg 5.732 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

