UKGMPMPCL

Ultra Low Loss, Singlemode MPO12 APC (unpinned) to MPO12 APC (unpinned) Fiber Trunk Cable Assembly, 96-Fiber, Armored Indoor Dual Rated (OFNR/LSZH)

Product Classification

Regional Availability	Asia | Australia/New Zealand | Europe | Latin America | Middle East /Africa | North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	SYSTIMAX ULL
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Connector A, quantity	8
Color, boot A	Black
Color, connector A	Lime green
Connector B, quantity	8
Color, boot B	Black
Color, connector B	Lime green
Construction Type	Armored | Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-12/UPC Female
Interface Feature, connector A	Unpinned
Interface, Connector B	MPO-12/UPC Female
Interface Feature, connector B	Unpinned
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	96

COMMSCOPE®

UKGMPMPCL

Dimensions

Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 – 999

Ordering Tree

BASE CODE	-	N	.	.	.	.	.

Jacket Color

J	Yellow

Breakout Length / Option

B	metal gland
C	with pulling grip
Z	36 inch extension with shelf mount, gland
Y	36 inch extension with shelf mount, gland, pulling grip
J	23 inch breakout, with mounting clips
K	23 inch breakout, with mounting clips, pulling grip both ends
R	23 inch breakout, with 36 inch extension, mounting clips
S	23 inch breakout, with 36 inch extension mounting clips, pulling grip both ends
L	23 inch breakout, with 72 inch extension mounting clips
M	23 inch breakout, with 72 inch extension, mounting clips, pulling grip both ends

Length

UOM

F	Feet
M	Meter

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °	4.40 lb @ 90 °

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®	OM5, LazrSPEED®

Environmental Specifications

COMMSCOPE®

UKGMPMPCL

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Dual Rated LSZH/Riser

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

COMMSCOPE®