4110273 | 2312V WTRL 1/2" PLEN TRUNK



75 Ohm P3® 500 JCAP 1/2" Plenum Trunk and Distribution Cable, white flame retardant PVC jacket

Product Classification

Product Type Coaxial hardline cable

Product Brand P3®

Warranty One year

General Specifications

Cable Type500 SeriesConstruction TypeSwagedJacket ColorWhite

Short Description P3 500 JCAP (2312V)

Dimensions

Cable Length731.52 m | 2400 ftDiameter Over Center Conductor, nominal2.769 mm | 0.109 inDiameter Over Dielectric, nominal11.481 mm | 0.452 inDiameter Over Jacket, nominal13.614 mm | 0.536 inDiameter Over Outer Conductor, nominal12.7 mm | 0.5 in

Jacket Thickness, nominal0.508 mm0.02 inOuter Conductor Thickness, nominal0.61 mm0.024 in

Electrical Specifications

Capacitance 52.493 pF/m | 16 pF/ft

dc Resistance Note Nominal values based on a standard condition of 20 °C (68 °F)

dc Resistance, Inner Conductor, nominal4.659 ohms/km | 1.42 ohms/kftdc Resistance, Loop, nominal5.873 ohms/km | 1.79 ohms/kft

Page 1 of 3



4110273 | 2312V WTRL 1/2" PLEN TRUNK

dc Resistance, Outer Conductor, nominal 1.214 ohms/km | 0.37 ohms/kft

Jacket Spark Test Voltage1000 VacNominal Velocity of Propagation (NVP)84 %

Structural Return Loss 20 dB @ 450-1000 MHz | 24 dB @ 5-450 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.62	0.19
10.0	0.85	0.26
50.0	2	0.61
85.0	2.23	0.68
100.0	2.98	0.91
200.0	4.49	1.37
204.0	3.51	1.07
400.0	7.12	2.17
700.0	10.53	3.21
900.0	12.2	3.72
1002.0	13.67	4.17
1218.0	15.91	4.85
1400.0	17.76	5.41
1500.0	18.76	5.72
1600.0	19.75	6.02
1700.0	20.74	6.32
1794.0	21.66	6.6
1800.0	21.72	6.62

Material Specifications

Center Conductor Material Copper-clad aluminum

Dielectric Material FFEP

Jacket Material Fire retardant PVC

Outer Conductor Material Aluminum

Mechanical Specifications

Minimum Bend Radius, standard 203.2 mm | 8 in

Pulling Tension, maximum 136.078 kg | 300 lb



4110273 | 2312V WTRL 1/2" PLEN TRUNK

Environmental Specifications

Environmental SpaceIndoor | PlenumTemperature Rating, UL75 °C | 167 °F

Flame Test Listing CATVP | CMP | NEC Article 820

Packaging and Weights

Packaging Type Reel

Weight, gross 235.13 kg/km | 158 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

