

# 760179960 | HFC-16SM-810-APE

---

HELIAX® Hybrid Cable with aluminum armor

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable, copper and fiber
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Application</b>	Remote radio head
<b>Armor Type</b>	Corrugated aluminum
<b>Cable Type</b>	Wireless feeder
<b>Conductors, quantity</b>	8
<b>Construction Type</b>	Armored
<b>Fiber Short Description</b>	RFF – 10AWG
<b>Fiber Type, quantity</b>	16
<b>Fibers per Subunit, quantity</b>	2
<b>Filler, quantity</b>	1
<b>Inner Shield (Tape) Material</b>	Corrugated aluminum
<b>Jacket Color</b>	Black
<b>Outer Shield (Tape) Material</b>	PE
<b>Strength Members</b>	Glass reinforced plastic rod
<b>Subunit, quantity</b>	8
<b>Total Fiber Count</b>	16
<b>Water Blocking Method</b>	Water blocking tape(s)   Water blocking threads

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	3.556 mm   0.14 in
<b>Diameter Over Jacket</b>	23.622 mm   0.93 in
<b>Conductor Gauge</b>	10 AWG

## Electrical Specifications

# 760179960 | HFC-16SM-810-APE


## dc Resistance Note

Maximum value based on a standard condition of 20 °C (68 °F)

## dc Resistance, maximum

3.412 ohms/km | 1.04 ohms/kft

## Representative Image



## Material Specifications

### Ripcord Material

Para-aramid synthetic fiber

## Mechanical Specifications

### Minimum Bend Radius, multiple bends, loaded

469.9 mm | 18.5 in

### Minimum Bend Radius, multiple bends, unloaded

236.22 mm | 9.3 in

### Minimum Bend Radius, single bend, unloaded

152.4 mm | 6 in

### Tensile Load, long term, maximum

800.68 N | 180 lbf

### Tensile Load, short term, maximum

2,668.932 N | 600 lbf

### Compression

2.25 kg/mm | 126 lb/in

### Compression Test Method

FOTP-41

### Flex Test Method

FOTP-104

### Impact

2.17 ft lb | 2.942 N-m

### Impact Test Method

FOTP-25

### Twist

10 cycles

### Twist Test Method

FOTP-85

## Optical Specifications

### Fiber Type

G.657.A2/B2 | G.657.A2/B2

## Environmental Specifications

# 760179960 | HFC-16SM-810-APE

---

<b>Installation temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Operating Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Storage Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Cable Qualification Standards</b>	ANSI/ICEA S-87-640   Telcordia GR-20   Telcordia GR-409
<b>Environmental Space</b>	Wireless installation

## Packaging and Weights

<b>Cable weight</b>	758.964 kg/km   510 lb/kft
---------------------	----------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## Included Products

CS-8G-MP	-	Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)
----------	---	--------------------------------------------------------------------------------------------------------

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

# CS-8G-MP

---

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Optical fiber

## General Specifications

<b>Cladding Diameter</b>	125 µm
<b>Cladding Diameter Tolerance</b>	±0.7 µm
<b>Cladding Non-Circularity, maximum</b>	0.7 %
<b>Coating Diameter (Colored)</b>	249 µm
<b>Coating Diameter (Uncolored)</b>	242 µm
<b>Coating Diameter Tolerance (Colored)</b>	±13 µm
<b>Coating Diameter Tolerance (Uncolored)</b>	±5 µm
<b>Coating/Cladding Concentricity Error, maximum</b>	12 µm
<b>Core/Clad Offset, maximum</b>	0.5 µm
<b>Proof Test</b>	689.476 N/mm <sup>2</sup>   100000 psi

## Dimensions

<b>Fiber Curl, minimum</b>	4 m   13.123 ft
----------------------------	-----------------

## Mechanical Specifications

<b>Macrobending, 15 mm mandrel, 1 turn</b>	0.50 dB @ 1,550 nm   1.00 dB @ 1,625 nm
<b>Macrobending, 20 mm mandrel, 1 turn</b>	0.10 dB @ 1,550 nm   0.20 dB @ 1,625 nm
<b>Macrobending, 30 mm mandrel, 10 turns</b>	0.03 dB @ 1,550 nm   0.10 dB @ 1,625 nm
<b>Coating Strip Force, maximum</b>	8.9 N   2.001 lbf
<b>Coating Strip Force, minimum</b>	1.3 N   0.292 lbf
<b>Dynamic Fatigue Parameter, minimum</b>	20

## Optical Specifications

<b>Cabled Cutoff Wavelength, maximum</b>	1260 nm
<b>Point Defects, maximum</b>	0.1 dB

# CS-8G-MP

<b>Zero Dispersion Slope, maximum</b>	0.092 ps/[km-nm-nm]
<b>Zero Dispersion Wavelength, maximum</b>	1324 nm
<b>Zero Dispersion Wavelength, minimum</b>	1302 nm

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	0.40 dB/km @ 1,310 nm   0.40 dB/km @ 1,385 nm   0.40 dB/km @ 1,550 nm   0.50 dB/km @ 1,625 nm
<b>Dispersion, maximum</b>	18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm
<b>Index of Refraction</b>	1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550 nm
<b>Mode Field Diameter</b>	8.6 $\mu\text{m}$ @ 1,310 nm   9.8 $\mu\text{m}$ @ 1,550 nm
<b>Mode Field Diameter Tolerance</b>	$\pm 0.4 \mu\text{m}$ @ 1310 nm   $\pm 0.5 \mu\text{m}$ @ 1550 nm
<b>Polarization Mode Dispersion Link Design Value, maximum</b>	0.06 ps/sqrt(km)
<b>Standards Compliance</b>	ITU-T G.657.A2   ITU-T G.657.B2

## Environmental Specifications

<b>Heat Aging, maximum</b>	0.05 dB/km @ 85 °C
<b>Temperature Dependence, maximum</b>	0.05 dB/km
<b>Temperature Humidity Cycling, maximum</b>	0.05 dB/km
<b>Water Immersion, maximum</b>	0.05 dB/km @ 23 °C

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

<b>Temperature Dependence, maximum</b>	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
<b>Temperature Humidity Cycling, maximum</b>	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity