A-100197

Base Product



Combiner/ Mast head amplifier enclosure for micro cell sites

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type	Micro cell site enclosure	
Ordering Note	For UK region only	

General Specifications

Access	Front door		
Batteries Supported	0		
Cabinet Type	Combiner cabinet		
Color	Green (RAL 6009) Light Gray (RAL 7035) Others available at additional cost		
Door Security	Swing handle with 22mm profile cylinder		
Doors, quantity	1		
Mounting	Plinth Root		
Dimensions			
Height	1143 mm 45 in		
Width	762 mm 30 in		

355.6 mm | 14 in

Electrical Specifications

Depth

Generator Connection	No connection
Rectifiers, quantity	0

Material Specifications

Finish	Powder coated	
Material Type	Galvanized steel	

Environmental Specifications

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 21, 2023



A-100197

Qualification Standards IEC 60529: 2001 | IEE Wiring Regulations BS 7671 | IP45

Packaging and Weights

Included	Brackets	Installation Kit
Included	Brackets	Installation Kit

 Weight, net
 49.895 kg | 110 lb

Regulatory Compliance/Certifications

Classification

Agency

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 21, 2023

