726774-000 | OCM1-CMB471L2



OCM1 LGX Fiber Optic Module, CWDM, Mux, LC/APC, 8 channels, upgrade port, starting wavelength 1470 nm

Product Classification

Regional AvailabilityNorth AmericaPortfolioCommScope®Product TypeCWDM moduleProduct SeriesLGX | OCM1

General Specifications

Device TypeStandard VAMFunctionalityMultiplexing

Technology Type Thin film filter (TFF)

Application For use with LGX panels

Circuits, quantity 1

Distribution Type 8-channel CWDM

Interface, frontLC/APCInterface, InputLC/APCInterface, OutputLC/APC

Multiplexers, quantity 1

Port Type, optional Upgrade port

Dimensions

 Height
 129.54 mm | 5.1 in

 Width
 27.94 mm | 1.1 in

 Depth
 127 mm | 5 in

Optical Specifications

Channel Spacing 20 nm **Starting Wavelength** 1470 nm

COMMSC PE°

726774-000 | OCM1-CMB471L2

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

