# MLOC-4-F1XM-HF-3M



HELIAX® M-LOC Multiport cluster 4 ports SureFlex® cable assembly with interface type M-LOC latching male to 4.3-10 female, size 1/4", length 3 meters

#### **Product Classification**

Product Type HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM

Product Brand HELIAX® | SureFlex®

Product Series MLOC

### General Specifications

Attachment, Connector A Factory attached

Attachment, Connector B Factory attached

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector AM-LOC Male

**Interface, Connector B** 4.3-10 Female

Specification Sheet Revision Level A

#### **Dimensions**

**Length** 3 m | 9.843 ft

Nominal Size 1/4 in

# **Electrical Specifications**

**3rd Order IMD Dynamic** -119 dBm

**3rd Order IMD Dynamic Test Method** Two +43 dBm carriers per IEC 62037

## VSWR/Return Loss

Frequency Band	Gated VSWR	Gated Return Loss (dB)	Insertion Loss, typical (dB)
1000-3000 MHz	1.07	30	1.18
3000-4200 MHz	1.11	26	1.42

Page 1 of 2



# MLOC-4-F1XM-HF-3M

**4200–5000 MHz** 1.12 25 1.56

Mechanical Specifications

Minimum Bend Radius, multiple Bends 25.4 mm | 1 in Minimum Bend Radius, single Bend 25.4 mm | 1 in

## **Environmental Specifications**

Installation temperature $-40 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )Operating Temperature $-55 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-67  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )Storage Temperature $-55 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-67  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**Immersion Test Method**Meets IEC 60529:2001, IP68 in mated condition

# Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



