

7698401-0002 | ION-U EU H 7P/80-85P/17P/19P-Vdc-M2



ION®-U High Power Extension Unit for USA700 and USA 750, SMR 800, CEL 850, AWS 1700, PCS 1900 Band Applications

OBSOLETE

Product Classification

Product Type Extension unit
Product Brand ION®-U

General Specifications

Note Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Type High

Electrical Specifications

Impedance 50 ohm
License Band AWS 1700 | CEL 850 | PCS 1900 | SMR 800 | USA 700 | USA 750
Voltage Range -60 to -48 Vdc

Electrical Specifications, Tx (Downlink)

Operating Frequency Band 1930 – 1995 MHz (PCS 1900) | 2110 – 2155 MHz (AWS 1700) | 728 – 746 MHz (USA 700) | 746 – 757 MHz (USA 750) | 862 – 869 MHz (SMR 800) | 869 – 894 MHz (CEL 850)