

Twin In-Band Diplexer, A CDMA/ B 850/700 LTE, DC sense

- Enables LTE carrier to share the RF path with other CDMA/EVDO services
- LTE port supports the use of dual band 700/850 radios or diplexed radio ports
- Narrow guard band to maximize utilization of licensed spectrum
- Automatic dc switching with dc sense

6 mm | 0.236 in

Product Classification

Product Type In-Band Combiner

Dimensions


 Height
 367 mm | 14.449 in

 Width
 300 mm | 11.811 in

 Depth
 142 mm | 5.591 in

Ground Screw Diameter

Outline Drawing



Electrical Specifications

5th Order IMD Test Method Two +43 dBm carriers

5th Order IMD, maximum -155 dBc

License Band CEL 850 | USA 700 | USA 750

Lightning Surge Current 10 kA

Lightning Surge Current Waveform 8/20 waveform

Electrical Specifications, Rx (Uplink)

Frequency Band 777 – 787 MHz | 835.5 – 849 MHz

Return Loss, minimum18 dBIsolation, minimum28 dB

Port Designation 700/850 LTE

COMMSCOPE®

Total Group Delay, maximum 120 ns

Electrical Specifications 2, Rx (Uplink)

Frequency Band 824.265 – 834.105 MHz

Group Delay Variation at Frequency, maximum 140 ns @ 1.25 MHz

Isolation, minimum 28 dB

Port Designation 850A-CDMA

Total Group Delay, maximum210 nsReturn Loss, minimum18 dB

Electrical Specifications, Tx (Downlink)

Frequency Band 746 – 756 MHz | 880.5 – 894 MHz

Isolation, minimum28 dBInput Power, PEP, maximum120 WInput Power, RMS, maximum1500 WTotal Group Delay, maximum120 nsReturn Loss, minimum18 dB

Electrical Specifications 2, Tx (Downlink)

Frequency Band 869.265 – 879.105 MHz

Group Delay Variation at Frequency, maximum 150 ns @ 1.25 MHz

Input Power, PEP, maximum120 WInput Power, RMS, maximum1500 WIsolation, minimum28 dBReturn Loss, minimum18 dBTotal Group Delay, maximum220 ns

Electrical Performance



Insertion Loss Specifications

850A-CDMA TO A	ANTENNA PORT	700/850B-LTE TO ANTENNA PORT					
Channels	Insetion Loss (dB)	Channels	Insetion Loss (dB)				
F1, F2, F3, F4, F5, F6, F7, F8	0.0 (Aug 1.251411-)	700MHz LTE	0.15 max				
F1, F2, F3, F4, F5, F6, F7, F8	0.9 max (AVg 1.25IVIH2)	850B LTE CH2560*	0.5 max				


^{*} Specifications are for the average of the freq. band

Frequency Map

700 MHz	 Α"	" А					В							A'	B'		
	1019	37	78	119	160	201	242	283	384	425	466	507	548	589	630	691	770
700 MHz	 F8	F7	F6	F5	F4	F3	F2	F1			2560	(10)	MHZ)			A'	F8

Legend Port 1 (LTE)
Port 2 (CDMA)
Guard Band

Block Diagram



Logic Table



DC inpu	t voltage	ANT Port				
LTE Port	CDMA Port	DC/AISG path selection				
<7	<7	All Ports OFF				
7 ≤ V ≤ 30	<7	LTE Port to ANT Port Of				
		CDMA Port to ANT OFF				
<7	7 ≤ V ≤ 30	LTE Port to ANT Port OFF				
</td <td>7 S V S 30</td> <td colspan="4">CDMA Port to ANT ON</td>	7 S V S 30	CDMA Port to ANT ON				
7 ≤ V ≤ 30	7 ≤ V ≤ 30	All Ports OFF				

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$

Ingress Protection Test Method IEC 60529:2001, IP67

Packaging and Weights

Weight, without mounting hardware 13 kg | 28.66 lb