

C4cTM CMTS Release 8.2.5



PRODUCT OVERVIEW:

The ARRIS C4c[™] CMTS is a compact DOCSIS® 3.0 platform based on the proven hardware and software of the larger C4® CMTS solution. It allows an operator to cost-effectively deploy DOCSIS, PacketCable[™], DSG/ADSG, and PacketCable Multimedia (PCMM[™]) services in small-to-medium size headends where space and power are often limited. The C4c CMTS supports DOCSIS 1.1/2.0/3.0 and PacketCable features, providing operators with a large array of Quality of Service capabilities to deploy revenue-generating services. Both AC-powered and DC-powered options are available. The following modules are supported:

- System Control Module (SCM), including support for the SCM II, SCM II EM, SCM II EM(U), and SCM 3
- Router Control Module (RCM)
- Downstream and Upstream Cable Access Modules (CAMs) 16D CAM, XD CAM, 12U CAM, 24U CAM





Release 8.2.5 delivers a significant set of value-added capabilities for C4c CMTS customers. With Rel. 8.2.5, cable operators deploying the C4c CMTS can utilize a 5 – 85 MHz band for the return frequency spectrum (24U CAM only) and also are able to bond up to eight (8) upstream channels (24U CAM only). Mulit-Protocol BGP routing support with the IPv6 Address Family is included in Rel. 8.2.5; this provides an important Layer 3 capability for operators deploying IPv6. Rel. 8.2.5 also supports marking the DiffServ Code Point (DSCP) for downstream subscriber traffic which allows MSOs to apply QoS principles within the subscriber premises. In addition, Rel. 8.2.5 supports a PCMM ECN which allows a single gate to use both an IPv4 and an IPv6 classifier; Rel. 8.2.5 also supports Password Challenge functionality for RADIUS Authentication.

FEATURES

- DSCP Marking for DHCP Packets
- PCMM ECN MM-N-13.0697-1 Support (IP4 and IPv6 Classifiers per Gate)
- DSCP Marking for Downstream Subscriber Traffic
- RADIUS Password Challenge
- Bonding of 8 US (24U CAM)
- Support for Multi-tuner Modems (without static RCCs)

- CLI Assignment for BSoD L2VPNs
- Annex A Mixed Modulation per F Connector
- 5 85 MHz Support (24U CAM)
- MP-BGP w/ IPv6 Address Family
- Intelligent TCS Assignment
- TCS Reduction
- MIB Support for Modem Count per Fiber Node

Copyright Statement: ©ARRIS Enterprises, Inc. 2015 All rights reserved. No part of this publication may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from ARRIS Enterprises, Inc. ("ARRIS"). ARRIS reserves the right to revise this publication and to make changes in content from time to time without obligation on the part of ARRIS to provide notification of such revision or change. ARRIS and the ARRIS logo are all trademarks of ARRIS Enterprises, Inc. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks and the names of their products. ARRIS disclaims proprietary interest in the marks and names of others.

Note: The capabilities, system requirements and/or compatibility with third-party products described herein are subject to change without notice.





Managing the C4c CMTS is typically done via the SNMP or CLI interfaces. The C4c CMTS has multiple options available for IPDR, a useful tool for measuring bandwidth usage. Physical maintenance of the C4c CMTS is very simple. Air filters should be inspected and/or replaced per recommendations in the C4c CMTS User Guides.

ONS
91 to 999 (DOCSIS° 3.0); 112 to 999 (EuroDOCSIS™ 3.0)
64, 256
30.34 to 55.62 per channel
41 to 60
5.361 (DOCSIS); 6.952 (EuroDOCSIS)
6 (DOCSIS), 8 (EuroDOCSIS)
75
-48 VDC (-44 to -72 VDC) 115/220 VAC (100 to 240 VAC, 47 to 63 Hz)
At -48 VDC: 900 W nominal and 1,200 W max At 115 VAC: 1,000 W nominal and 1,350 W max
+23 to +131 (-5 to +55)
+41 to +104 (+5 to +40)
C) -40 to +158 (-40 to +70)
5 to 85% (Non condensing)
12.25 x 18.05 x 22.5 (31.1 x 44.3 x 57.2)
116.2 (52.7)

RF Upstream			
Frequency Range (MHz)		5 to 85 MHz (24U CAM) 5 to 65 MHz (12U CAM)	
Modulation		QPSK, 16 QAM, 32 QAM, 64 QAM	
Channel Type		TDMA, ATDMA, TDMA/ATDMA	
Data Rate (Mbps) (Max.)		30.72 per channel	
RF Input Level (dBmV)		-16 to +29	
Frequency Resolution (KHz)		<1	
Installation Environ	ment		
Management Interfaces		.00/1000 Mbps Ethernet (RJ-45) plus Console al port, RJ45)	
Network-side Interfaces	10 G	igabit Ethernet (SFP+) auto-baud, eight per card	
Connector Access		Ethernet ports via front of chassis, management s via rear	
Management Acces	s		
In-band Managemer	nt with	Access Control Lists via any NSI port	
Out-of-Band Management via dedicated Ethernet port on SCM			
Console (serial) port	on SC	M PIC	





The C4c CMTS provides cable operators with significant improvements in DC power consumption per downstream channel as compared to other compact DOCSIS 3.0 platforms. This leads to reduced powering and cooling requirements for the operators' facilities, which can provide savings in operational and capital expenditures.

SOFTWARE RELEASE 8.2.5 FEATURES (PARTIAL LISTING)		
DSCP Marking for DHCP Packets	IPv6 Support, Including:	
PCMM ECN Support (IP4 and IPv6 Classifiers per Gate)	IS-IS Multi-Topology Support	
DSCP Marking for Downstream Subscriber Traffic	OSPFv3	
RADIUS Password Challenge	DHCPv6 Prefix Delegation with Route Injection	
Bonding of 8 US (24U CAM)	Cable Source Verify with DHCP Lease Query	
Support for Multi-tuner Modems (without static RCCs)	TFTP Enforce & Dynamic Shared Secret for IPv6 CMs	
CLI Assignment for BSoD L2VPNs	DOCSIS 3.0 Multicast IP Video Support (via IGMPv3)	
Annex A Mixed Modulation per F Connector	Multicast CAC for IP Video (Phase 1)	
5 – 85 MHz Support (24U CAM)	Policy-Based Routing with Recursive Next Hop	
MP-BGP w/ IPv6 Address Family	Dynamic CM Load Balancing, including Cross-MAC Domain	
Intelligent TCS Assignment	16D CAM, XD CAM	
TCS Reduction	12U CAM, 24U CAM	
MIB Support for Modem Count per Fiber Node	BSoD L2 VPN	
Ethernet Link Aggregation (1 Gbps ports)	BPI+ Enforce	
Integrated Service Class Agility	TFTP Enforce and Dynamic Shared Secret	
IPv6 Support for PCMM	Integrated Upstream Agility	
Load Balancing of D3.0 Voice Flows (DS and US)	PIM-SSM, IGMPv2, and static multicast	
DSG 3.0	RIPv2 (RFC 1723), OSPFv2 (RFC 2328), IS-IS, BGPv4	
Extended CM Transmit Power (for USCB)	SII Lawful Intercept (RFC 3924)	
802.1Q VLAN tagging		

ORDERING INFORMATION			
780151	C4c Chassis, 8 Slot Chassis Assembly – 7 RU Chassis		
780271	C4c AC Power Supply Module		
780272	C4c DC Power Supply Module		
708369	Physical Interface Card (PIC) for the SCM with Fan Controller		
793931	System Control Module II Enhanced Memory (Updated) (SCM II EM(U))		
722013	Router Control Module (RCM)		
794046	Optimized 16D Cable Access Module (CAM) Kit (Active) Licensed for 16 Downstreams, DOCSIS/EuroDOCSIS 3.0		
794048	Optimized 24D Cable Access Module (CAM) Kit (Active) Licensed for 24 Downstreams, EuroDOCSIS 3.0		
794047	Optimized 32D Cable Access Module (CAM) Kit (Active) Licensed for 32 Downstreams, DOCSIS 3.0		
794069	24U CAM Kit (Even) – 24U CAM, Even CAM PIC, and 24 Upstream Licenses, DOCSIS/EuroDOCSIS 3.0		
794070	24U CAM Kit (Odd) – 24U CAM, Odd CAM PIC, and 24 Upstream Licenses, DOCSIS/EuroDOCSIS 3.0		
782360	C4c CMTS Rel. 8.2 DOCSIS 3.0 License per Downstream for 16D/XD CAM		
782361	C4c CMTS Rel. 8.2 DOCSIS 3.0 License per Upstream for 12U/24U CAM		
708387	Software Maintenance - Phone Plus Gold (Required)		

Full price list available from ARRIS.

Copyright Statement: @ARRIS Enterprises, Inc. 2015 All rights reserved. No part of this publication may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from ARRIS Enterprises, Inc. ("ARRIS"). ARRIS reserves the right to revise this publication and to make changes in content from time to time without obligation on the part of ARRIS to provide notification of such revision or change. ARRIS and the ARRIS logo are all trademarks of ARRIS Enterprises, Inc. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks and the names of their products. ARRIS disclaims proprietary interest in the marks and names of others.

Note: The capabilities, system requirements and/or compatibility with third-party products described herein are subject to change without notice.