F1PNF



Type N Female for 1/4 in FSJ1-50A cable

Product Classification

Product TypeWireless and radiating connector

Product Brand HELIAX®
Product Series FSJ1-50A

General Specifications

Body StyleStraightCable FamilyFSJ1-50AInner Contact Attachment MethodSolderInner Contact PlatingGold

InterfaceN FemaleMounting AngleStraight

Outer Contact Attachment Method Self-clamping

Outer Contact PlatingSilverPressurizableNo

Dimensions

 Height
 15.75 mm | 0.62 in

 Width
 15.75 mm | 0.62 in

 Length
 55.12 mm | 2.17 in


 Diameter
 15.75 mm | 0.62 in

Nominal Size 1/4 in

Outline Drawing



F1PNF



Electrical Specifications

3rd Order IMD at Frequency-112 dBm @ 910 MHz3rd Order IMD Test MethodTwo +43 dBm carriersAverage Power at Frequency0.4 kW @ 900 MHz

Cable Impedance50 ohmConnector Impedance50 ohmdc Test Voltage1600 VInner Contact Resistance, maximum1 mOhmInsulation Resistance, minimum5000 MOhmOperating Frequency Band0 - 8000 MHzOuter Contact Resistance, maximum0.25 mOhm

Peak Power, maximum6.4 kWRF Operating Voltage, maximum (vrms)565 VShielding Effectiveness-110 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
45-4100 MHz	1.119	25.01
4100-6200 MHz	1.173	21.98

COMMSCOPE®

FIPNE

6200–11000 MHz 1.433 14.99

Mechanical Specifications

Connector Retention Tensile Force 449.27 N | 101 lbf

Coupling Nut Proof Torque 1.7 N-m | 15.046 in lb

Coupling Nut Proof Torque Method IEC 61169-16:9.3.11

Coupling Nut Retention Force 445 N | 100.04 lbf

Coupling Nut Retention Force Method IEC 61169-16:9.3.11

Insertion Force 124.55 N | 28 lbf

Insertion Force Method IEC 61169-16:9.3.5

Interface Durability 500 cycles

Interface Durability Method IEC 61169-4:17

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-67 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature -65 °C to +125 °C (-85 °F to +257 °F)

Attenuation, Ambient Temperature 20 °C | 68 °F

Average Power, Ambient Temperature 40 °C | 104 °F

Average Power, Inner Conductor Temperature 100 °C | 212 °F

Corrosion Test Method IEC 60068-2-11

Immersion Depth 1 m

Immersion Test Mating Mated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net 100.46 g | 0.221 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

F1PNF

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Immersion Depth Immersion at specified depth for 24 hours

