## F1TNM-HC



### Type N Male for 1/4 in FSJ1-50A cable

### **Product Classification**

**Product Type**Wireless and radiating connector

Product Brand HELIAX®
Product Series FSJ1-50A

### General Specifications

Body StyleStraightCable FamilyFSJ1-50AInner Contact Attachment MethodCaptivated

Inner Contact PlatingSilverInterfaceN MaleMounting AngleStraight

 Outer Contact Attachment Method
 Self-clamping

 Outer Contact Plating
 Trimetal

Pressurizable No

### **Dimensions**


 Length
 48.01 mm | 1.89 in

 Diameter
 20.32 mm | 0.8 in

Nominal Size 1/4 in

### Outline Drawing





### **Electrical Specifications**

**3rd Order IMD at Frequency** -116 dBm @ 910 MHz

**3rd Order IMD Test Method**Two +43 dBm carriers

Average Power at Frequency 0.4 kW @ 900 MHz

Cable Impedance 50 ohm

Connector Impedance 50 ohm

dc Test Voltage 1600 V

 Inner Contact Resistance, maximum
 1 mOhm

 Insulation Resistance, minimum
 5000 MOhm

Insulation Resistance, minimum 5000 MOhm

Operating Frequency Band 0 - 6000 MHz

Outer Contact Resistance, maximum 0.25 mOhm

Peak Power, maximum 6.4 kW

**RF Operating Voltage, maximum (vrms)** 565 V

**Shielding Effectiveness** -110 dB

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

**COMMSCOPE®** 

## F1TNM-HC

450-2200 MHz	1.065	30.04
2200-3000 MHz	1.065	30.04
3000-6000 MHz	1.18	21.67

#### Mechanical Specifications

Connector Retention Tensile Force449.27 N | 101 lbfCoupling Nut Proof Torque1.7 N-m | 15.046 in lbCoupling Nut Proof Torque MethodIEC 61169-16:9.3.11Coupling Nut Retention Force449.98 N | 101.16 lbfCoupling Nut Retention Force MethodIEC 61169-16:9.3.11Insertion Force124.55 N | 28 lbfInsertion Force MethodIEC 61169-16:9.3.5

Interface Durability500 cyclesInterface Durability MethodIEC 61169-4:17Mechanical Shock Test MethodIEC 60068-2-27

### **Environmental Specifications**

Operating Temperature $-55 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-67  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )Storage Temperature $-65 \,^{\circ}\text{C}$  to  $+125 \,^{\circ}\text{C}$  (-85  $^{\circ}\text{F}$  to  $+257 \,^{\circ}\text{F}$ )

Attenuation, Ambient Temperature20 °C | 68 °FAverage Power, Ambient Temperature40 °C | 104 °FAverage Power, Inner Conductor Temperature100 °C | 212 °FCorrosion Test MethodIEC 60068-2-11

Immersion Depth1 mImmersion Test MatingMated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test MethodIEC 60068-2-3Thermal Shock Test MethodIEC 60068-2-14Vibration Test MethodIEC 60068-2-6

Packaging and Weights

**Weight, net** 43.83 g | 0.097 lb

Regulatory Compliance/Certifications



# F1TNM-HC

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

**Immersion Depth** Immersion at specified depth for 24 hours

