MGS600

Base Product



GigaSPEED X10D® M-Series Modular Jack, RJ45, Cat6A Unshielded

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio SYSTIMAX®

Product Type Modular jack

Product Brand GigaSPEED X10D®

Product Series MGS600

General Specifications

ANSI/TIA Category 6A

Cable Type Unshielded

Conductor Type Solid | Stranded

Termination Type IDC

Wiring T568A | T568B

Dimensions

Height 19.4 mm | 0.764 in

Width 21.08 mm | 0.83 in

Depth 30.2 mm | 1.189 in

Compatible Conductor Gauge, solid 22 AWG | 24 AWG

Compatible Conductor Gauge, stranded 22 AWG | 24 AWG

Electrical Specifications

 Contact Resistance Variation, maximum
 20 mOhm

 Contact Resistance, maximum
 100 mOhm

Page 1 of 2



MGS600

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

PoE Durability

Supports IEEE 802.3bt Type 4 (90 W) applications after 3000

plug to jack mating cycles

Material Specifications

Contact Plating Material Precious metals

Material Type Copper alloy | High-impact, flame retardant, thermoplastic

Termination Contact Plating Nickel

Mechanical Specifications

Plug Retention Force, minimum 133 N | 29.9 lbf

Plug to Jack Mating Cycles Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative HumidityUp to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

