760246203 | OCAB-P-I3-INW-72F



OCAB Outdoor fiber distribution cabinet - innerwork

Cabinet innerwork for up to 72f customer connections

- \cdot 48 up to 72 Point-to-multipoint positions, SC & LC footprint
- · 8 branch-off blown fibre Ø5,7& 8mm microtube positions
- \cdot 4 branch-off blown fibre Ø 12mm microtube positions
- \cdot 72 direct drops blown fibre Ø5,7 & 8mm microtube positions
- \cdot Up to 10 OCM1 LGX Style Fiber Optic Splitter Module positions
- \cdot Transient-free, modular, flexible fibre management \cdot
- \cdot FIST single-circuit and single-element splice trays
- \cdot Up to 480 splices (including SC trays 160 splices)
- \cdot Storage area for looped cable
- \cdot Compatible with all fibre types: G.652D and G.657 series

Product Classification

| Regional Availability | EMEA |
|-----------------------|-------------------------|
| Product Type | Fiber cross-connect hub |
| Product Series | OCAB |

General Specifications

| Color | Light Gray (RAL 7035) | | |
|----------|-----------------------|--|--|
| Mounting | Cabinet | | |

Dimensions

| Height | 825 mm | Ι | 32.48 in |
|--------|--------|---|-----------|
| Width | 436 mm | Ι | 17.165 in |
| Depth | 222 mm | I | 8.74 in |

Material Specifications

Finish

Powder coated polyester

Packaging and Weights

| Packaging quantity | 8 |
|--------------------|--------|
| Packaging Type | Pallet |

Page 1 of 2

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: May 29, 2021



760246203 | OCAB-P-I3-INW-72F

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant



ROHS

Page 2 of 2

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: May 29, 2021

