

Quad Diplexer, 380-960 MHz/1695-2690 MHz,dc Sense,4.3-10

- BTS-to-feeder and feeder-to-antenna application
- New 4.3-10 connectors for improved PIM performance and size reduction
- Automatic dc switching with dc sense
- Convertible mounting brackets

Product Classification

Product Type Diplexer

General Specifications

Product Family CBC426
Color Gray
Common Port Label ANT
Modularity 4-Quad

MountingPole| WallMounting Pipe HardwareBand clamps (2)RF Connector Interface4.3-10 FemaleRF Connector Interface Body StyleLong neck

Dimensions

 Height
 152 mm | 5.984 in

 Width
 121 mm | 4.764 in


 Depth
 182 mm | 7.165 in

 Ground Screw Diameter
 6 mm | 0.236 in

 Mounting Pipe Diameter Range
 40-160 mm

Outline Drawing





Electrical Specifications

Impedance 50 ohm

License Band, Band Pass APT 700 | AWS 1700 | CEL 850 | CEL 900 | DCS 1800 | EDD 800 | IMT

2100 | IMT 2600 | LMR 750 | LMR 800 | LMR 900 | PCS 1900 | TDD

1900 | TDD 2000 | TDD 2300 | TDD 2600 | USA 600 | USA 700 | USA 750

Electrical Specifications, Common Port

250 W **Composite Power, RMS**

Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through Method Auto sensing dc/AISG Pass-through Path See logic table

Lightning Surge Current 10 kA



Lightning Surge Current Waveform 8/20 waveform

Voltage 7–30 Vdc

Electrical Specifications, AISG

AISG Carrier 2176 KHz ± 100 ppm

Insertion Loss, maximum1 dBReturn Loss, minimum15 dB


Electrical Specifications

| Sub-module | 1 2 3 4 | 1 2 3 4 |
|------------------|--|--|
| Branch | 1 | 2 |
| Port Designation | 380-960 | 1695-2690 |
| License Band | LMR 750, Band Pass LMR 800, Band Pass USA 700, Band Pass USA 750, Band Pass USA 600, Band Pass CEL 850, Band Pass | PCS 1900, Band Pass WCS 2300, Band Pass AWS 1700, Band Pass TDD 2600, Band Pass |

Electrical Specifications, Band Pass

| Frequency Range, MHz | 380-960 | 1695-2690 |
|--------------------------------|-------------------|-------------------|
| Insertion Loss, typical, dB | 0.1 | 0.1 |
| Total Group Delay, typical, ns | 2 | 4 |
| Return Loss, typical, dB | 24 | 22 |
| Isolation, typical, dB | 65 | 63 |
| Input Power, RMS, maximum, W | 200 | 200 |
| Input Power, PEP, maximum, W | 2000 | 2000 |
| 3rd Order PIM, minimum, dBc | -161 | -161 |
| 3rd Order PIM Test Method | 2 x 20 W CW tones | 2 x 20 W CW tones |

Block Diagram





Logic Table

| Combining Mode Operation (Ground Based) | | round Based) | |
|---|------------------|--------------|---------------------------------|
| RF Ports Input DC Voltage | | tage | |
| 380 to 960 MHz | 1695 to 2690 MHz | COMMON | DC/AISG Path Selection |
| 7 ≤ V ≤ 30 | <7 | <7 | 380 to 960 MHz to COMMON "ON" |
| <7 | 7 ≤ V ≤ 30 | <7 | 1695 to 2690 MHz to COMMON "ON" |
| 7 ≤ V ≤ 30 | 7 ≤ V ≤ 30 | <7 | 1695 to 2690 MHz to COMMON "ON" |

| Splitting Mode Operation (Tower Top) | | ower Top) | |
|--------------------------------------|------------------|-------------|--------------------------|
| RF Ports Impedance DC (Load sensing) | | ad sensing) | |
| 380 to 960 MHz | 1695 to 2690 MHz | COMMON | DC/AISG Path Selection |
| open/load | short | 7 ≤ V ≤ 30 | COMMON to 380-960 "ON" |
| short | open/load | 7 ≤ V ≤ 30 | COMMON to 1695-2690 "ON" |
| open/load | open/load | 7 ≤ V ≤ 30 | ALL ports ON |
| short | short | 7 ≤ V ≤ 30 | ALL ports OFF |

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \left(-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F}\right)$

Relative Humidity 5%-100%

Corrosion Test Method IEC 60068-2-11, 30 days

Ingress Protection Test Method IEC 60529:2001, IP67

Packaging and Weights

IncludedMounting hardwareMounting Hardware Weight0.6 kg | 1.323 lb

Volume 3.35 L

Weight, without mounting hardware 5.4 kg | 11.905 lb