

JM-CAPKIT



2.2-5 Male End Cap Assembly


Product Classification

Product Type	Wireless connector accessory
Product Brand	HELIAX®

Dimensions

Length	22.5 mm 0.886 in
Diameter	13.96 mm 0.55 in

Outline Drawing



Material Specifications

Finish	Trimetal
---------------	----------

JM-CAPKIT

Material Type Brass

Mechanical Specifications

Coupling Nut Proof Torque 4 N-m | 35.403 in lb

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Storage Temperature -65 °C to +125 °C (-85 °F to +257 °F)

Corrosion Test Method IEC 60068-2-11

Immersion Depth 1 m

Immersion Test Mating Mated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Packaging quantity 1

Weight, net 18.36 g | 0.04 lb

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

* Footnotes

Immersion Depth Immersion at specified depth for 24 hours