SF-HPM3-B



Heavy Duty Square T-Arm Base Kit for 2–7/8 in OD face pipe supports, pipe ordered separately

Product Classification

Product TypeCo-location dual pipe mount kit

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

Pipe, quantity 0

Tower Taper Non-tapered | Tapered

Dimensions

Height 355.6 mm | 14 in

Face Width $1.676 \text{ m} \mid 5.5 \text{ ft}$

Width 1,676.4 mm | 66 in

Length 609.6 mm | 24 in

Mounting Diameter, maximum 203.2 mm | 8 in

Mounting Diameter, minimum 0 mm | 0 in

Pipe Outer Diameter73.66 mm | 2.9 in

Stand-off Distance 508 mm | 20 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Clamps | Frame | Pipe mounts | Saddle mounts

Page 1 of 2

SF-HPM3-B

Packaging quantity

Weight, net 83.007 kg | 183 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

1

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

