

# NG4-VMMRF4H



NG4access® Module VAM, Monitoring, 70/30, singlemode, LC/APC, front, right, 4 circuits

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers
- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Monitoring module
<b>Product Brand</b>	NG4access®
<b>Product Series</b>	FACT   NG4
<b>Government Funding</b>	Build America Buy America (BABA) compliant*

## General Specifications

<b>Device Type</b>	Plug-and-play module
<b>Functionality</b>	Monitoring
<b>Access</b>	Front
<b>Application</b>	For use with NG4 access frames
<b>Circuits, quantity</b>	4
<b>Distribution Type</b>	1 x 2 splitter
<b>Interface, front</b>	LC/APC
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Split Ratio</b>	70/30
<b>Splitter, quantity</b>	4
<b>Tray Orientation</b>	Right orientation

# NG4-VMMRF4H

---

## Dimensions

<b>Height</b>	13.21 mm   0.52 in
<b>Width</b>	159.77 mm   6.29 in
<b>Depth</b>	130.3 mm   5.13 in

## Optical Specifications

<b>Directivity, minimum</b>	50 dB
<b>Polarization Dependent Loss, maximum</b>	0.2 dB
<b>Insertion Loss, Primary Output, maximum</b>	2.9 dB
<b>Insertion Loss, Secondary Output, maximum</b>	6.9 dB
<b>Return Loss, Splitter, minimum</b>	50 dB

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---